

Featured

- 1204 1.85mm SMD LED
- High Brightness
- AlInGaP / InGaN Technology
- Narrow View Angle
- High Reliability
- Clear Lens

Applications

- Consumer Electronics
- Wearables
- Automobile After Market
- Industrial Equipment

Description

The IN-S124BR series is a popular 1204 package with reverse mount and versatile design capabilities. It is a PCB type molding style LED which can be used in various applications.

Recommended Solder Pattern




Figure 1. IN-S124BR Solder Pattern

Package Dimensions in mm




Figure 2. IN-S124BR Package Dimensions

Absolute Maximum Rating at 25°C (Note 1)

| Product | Emission Color | P_d (mW) | I_F (mA) | I_{FP}^* (mA) | V_R (V) | T_{OP} (°C) | T_{ST} (°C) |
|-------------|----------------|------------|------------|-----------------|-----------|---------------|---------------|
| IN-S124BRYG | Yellow Green | 48 | 20 | 30 | 5 | -40°C~+85°C | -40°C~+100°C |
| IN-S124BRY | Yellow | | | | | | |
| IN-S124BRA | Amber | | | | | | |
| IN-S124BRR | Red | | | | | | |
| IN-S124BRB | Blue | 78 | 20 | 60 | 5 | -40°C~+85°C | -40°C~+100°C |
| IN-S124BRG | Green | | | | | | |
| IN-S124BRUW | White | | | | | | |

Notes

1. Condition for IFP is pulse of 1/10 duty and 0.1msec width

ESD Precaution

ATTENTION: Electrostatic Discharge (ESD) protection



The symbol above denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are STATIC SENSITIVE devices. ESD precaution must be taken during design and assembly. If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.

Please be advised that normal static precautions should be taken in the handling and assembly of this device to prevent damage or degradation which may be induced by electrostatic discharge (ESD).

Electrical Characteristics $T_A = 25^\circ\text{C}$ (Note 1)

| Product | Emission Color | $I_F(\text{mA})$ | $V_F(\text{V})$ | | $\lambda(\text{nm})$ | | | Viewing Angle | $I^*_v(\text{mcd})$ |
|-------------|----------------|------------------|-----------------|-----|----------------------|-------------|-----------------|-----------------|---------------------|
| | | | typ. | max | λ_D | λ_P | $\Delta\lambda$ | $2\theta_{1/2}$ | typ. |
| IN-S124BRYG | Yellow Green | 20 | 2.1 | 2.4 | 571 | 573 | 15 | 20 | 715.0 |
| IN-S124BRY | Yellow | 20 | 2.0 | 2.4 | 589 | 591 | 20 | 20 | 1125.0 |
| IN-S124BRA | Amber | 20 | 2.0 | 2.4 | 605 | 609 | 17 | 20 | 1800.0 |
| IN-S124BRR | Red | 20 | 2.0 | 2.4 | 624 | 632 | 20 | 20 | 900.0 |
| IN-S124BRB | Blue | 20 | 3.3 | 3.9 | 470 | 468 | 40 | 20 | 715.0 |
| IN-S124BRG | Green | 20 | 3.3 | 3.9 | 525 | 520 | 30 | 20 | 1440.0 |
| IN-S124BRUW | White | 20 | 3.3 | 3.9 | X=0.29 Y=0.29 | - | - | 20 | 715.0 |

Notes

1. Performance guaranteed only under conditions listed in above tables.


Chromaticity Bin (for White only)





| | Rank C1 | | | |
|---|---------|--------|--------|--------|
| x | 0.2500 | 0.2700 | 0.2700 | 0.2500 |
| y | 0.2500 | 0.2775 | 0.2325 | 0.2050 |

| | Rank C2 | | | |
|---|---------|--------|--------|--------|
| x | 0.2700 | 0.2900 | 0.2900 | 0.2700 |
| y | 0.2775 | 0.3050 | 0.2600 | 0.2325 |




| | Rank D1 | | | |
|---|---------|--------|--------|--------|
| x | 0.2900 | 0.3100 | 0.3100 | 0.2900 |
| y | 0.3050 | 0.3325 | 0.2875 | 0.2600 |


| | Rank D2 | | | |
|---|---------|--------|--------|--------|
| x | 0.3100 | 0.3300 | 0.3300 | 0.3100 |
| y | 0.3325 | 0.3600 | 0.3150 | 0.2875 |




Typical Characteristic Curves – YG, Y, A, R


Typical Characteristic Curves – B, G, W



Typical Characteristic Curves – Radiation Pattern

Ordering Information


| Product | Emission Color | Technology | Test Current I_F (mA) | Luminous Intensity I_V (mcd) (Typ.) | Forward Voltage V_F (V) (Typ.) | Orderable Part Number |
|-------------|----------------|------------|-------------------------|---------------------------------------|----------------------------------|-----------------------|
| IN-S124BRYG | Yellow Green | AlInGaP | 20 | 715.0 | 2.1 | IN-S124BRYG |
| IN-S124BRY | Yellow | AlInGaP | 20 | 1125.0 | 2.0 | IN-S124BRY |
| IN-S124BRA | Amber | AlInGaP | 20 | 1800.0 | 2.0 | IN-S124BRA |
| IN-S124BRR | Red | AlInGaP | 20 | 900.0 | 2.0 | IN-S124BRR |
| IN-S124BRB | Blue | InGaN | 20 | 715.0 | 3.3 | IN-S124BRB |
| IN-S124BRG | Green | InGaN | 20 | 1440.0 | 3.3 | IN-S124BRG |
| IN-S124BRUW | White | InGaN | 20 | 715.0 | 3.3 | IN-S124BRUW |

Label Specifications

Inolux P/N:

| I | N | - | S | 1 | 2 | 4 | B | R | | | X | - | X | X | X | X | |
|--------|-----|---|--------------|---------------------------|---|---|-----------|-------------------|----------------|---------------------------------|--|---|----------------------|---|---|---|--|
| | | | Material | Package | | | Variation | Orientation | Current | Lens | Color | | Customized Stamp-off | | | | |
| Inolux | SMD | | S = PCB Type | 124B = 3.2 x 1.6 x 1.85mm | | | | R = Reverse Mount | (Blank) = 20mA | (Blank) = Clear U = Diffused | R=624nm A=605nm Y=589nm YG=571nm G=525nm B=470nm W=White | | | | | | |


Lot No.:


| | | | | | | | |
|------------------|--------------------------|---|---|---|-------|------|--------|
| Z | 2 | 0 | 1 | 7 | 01 | 24 | 001 |
| Internal Tracker | Year (2017, 2018,) | | | | Month | Date | Serial |

Packaging Information: 2000pcs Per Reel
Tape Dimension


| Part No. | Dim. A | Dim. B | Dim. C | Q'ty/Reel |
|-----------|-----------|-----------|-----------|-----------|
| IN-S124BR | 3.37±0.10 | 1.78±0.10 | 2.17±0.10 | 2K |

Unit: mm

Reel Dimension


Packing Dimension


5 boxes per carton are available depending on shipment quantity.

| | Specification | Material | Quantity |
|--------------|----------------------|-----------------------------------|------------------|
| Carrier tape | Per EIA 481-1A specs | Conductive black tape | 4000pcs per reel |
| Reel | Per EIA 481-1A specs | Conductive black | |
| Label | IN standard | Paper | |
| Packing bag | 220x240mm | Aluminum laminated bag/ no-zipper | One reel per bag |
| Carton | IN standard | Paper | Non-specified |

Others:


Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, λD and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

Upon request, a humidity indicator will be included in the moisture protected anti-static bag prior to shipment.


The packaging sequence is as follows:



Reflow Soldering

- Recommended tin glue specifications: melting temperature in the range of 178~192 °C
- The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):

Lead-free Solder Profile



Precautions

- Avoid exposure to moisture at all times during transportation or storage.
- Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
- It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage.
- Avoid operation beyond the limits as specified by the absolute maximum ratings.
- Avoid direct contact with the surface through which the LED emits light.
- If possible, assemble the unit in a clean room or dust-free environment.

Reworking

- Rework should be completed within 5 seconds under 260 °C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100 °C max, <3min

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electro-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Reliability

| Item | Frequency/ lots/ samples/ failures | Standards Reference | Conditions |
|--------------------------------------|---|--------------------------------|--|
| Precondition | For all reliability monitoring tests according to JEDEC Level 2 | J-STD-020 | 1.) Baking at 85°C for 24hrs 2.) Moisture storage at 85°C/ 60% R.H. for 168hrs |
| Solderability | 1Q/ 1/ 22/ 0 | JESD22-B102-B And CNS-5068 | Accelerated aging 155°C/ 24hrs Tinning speed: 2.5+0.5cm/s Tinning: A: 215°C/ 3+1s or B: 260°C/ 10+1s |
| Resistance to soldering heat | | CNS-5067 | Dipping soldering terminal only Soldering bath temperature A: 260+/-5°C; 10+/-1s B: 350+/-10°C; 3+/-0.5s |
| Operating life test | 1Q/ 1/ 40/ 0 | CNS-11829 | 1.) Precondition: 85°C baking for 24hrs 85°C/ 60%R.H. for 168hrs 2.) Tamb25°C; IF=20mA; duration 1000hrs |
| High humidity, high temperature bias | 1Q/ 1/ 45/ 0 | JESD-A101-B | Tamb: 85°C Humidity: 85% R.H., IF=5mA Duration: 1000hrs |
| High temperature bias | 1Q/ 1/ 20 | IN specs. | Tamb: 55°C IF=20mA Duration: 1000hrs |
| Pulse life test | 1Q/ 1/ 40/ 0 | | Tamb25°C, If=20mA,, Ip=100mA, Duty cycle=0.125 (tp=125 μ s, T=1sec) Duration 500hrs) |
| Temperature cycle | 1Q/ 1/ 76/ 0 | JESD-A104-A IEC 68-2-14, Nb | A cycle: -40 degree C 15min; +85 degree C 15min Thermal steady within 5 min.. 300 cycles 2 chamber/ Air-to-air type |
| High humidity storage test | 1Q/ 1/ 40/ 0 | CNS-6117 | 60+3°C 90+5/-10% R.H. for 500hrs |
| High temperature storage test | 1Q/ 1/ 40/ 0 | CNS-554 | 100+10°C for 500hrs |
| Low temperature storage test | 1Q/ 1/ 40/ 0 | CNS-6118 | -40+5°C for 500hrs |

Revision History

| Changes since last revision | Page | Version No. | Revision Date |
|-----------------------------|------|-------------|---------------|
| Initial Release | | 1.0 | 04-10-2017 |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |
| | | | |

DISCLAIMER

INOLUX reserves the right to make changes without further notice to any products herein to improve reliability, function or design. INOLUX does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

LIFE SUPPORT POLICY

INOLUX's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of INOLUX or INOLUX CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



Стандарт Электрон Связь

Мы молодая и активно развивающаяся компания в области поставок электронных компонентов. Мы поставляем электронные компоненты отечественного и импортного производства напрямую от производителей и с крупнейших складов мира.

Благодаря сотрудничеству с мировыми поставщиками мы осуществляем комплексные и плановые поставки широчайшего спектра электронных компонентов.

Собственная эффективная логистика и склад в обеспечивает надежную поставку продукции в точно указанные сроки по всей России.

Мы осуществляем техническую поддержку нашим клиентам и предпродажную проверку качества продукции. На все поставляемые продукты мы предоставляем гарантию .

Осуществляем поставки продукции под контролем ВП МО РФ на предприятия военно-промышленного комплекса России , а также работаем в рамках 275 ФЗ с открытием отдельных счетов в уполномоченном банке. Система менеджмента качества компании соответствует требованиям ГОСТ ISO 9001.

Минимальные сроки поставки, гибкие цены, неограниченный ассортимент и индивидуальный подход к клиентам являются основой для выстраивания долгосрочного и эффективного сотрудничества с предприятиями радиоэлектронной промышленности, предприятиями ВПК и научно-исследовательскими институтами России.

С нами вы становитесь еще успешнее!

Наши контакты:

Телефон: +7 812 627 14 35

Электронная почта: sales@st-electron.ru

Адрес: 198099, Санкт-Петербург,
Промышленная ул, дом № 19, литера Н,
помещение 100-Н Офис 331